

Patient Lifting Solutions bv Arkeneel 27 3905 NS Veenendaal The Netherlands

Datasheet Turntable HD 3-Way and 4-Way (1001-HD/1002-HD)	
Functions	Value/unit/description
Maximum operation capacity (Ceiling Hoist)	350 kg
Installation	PLS Rail A-Profile (standard) and B-Profile in combination with a console.
Operation (input)	2x Reed Sensor activated by magnets on Trolley of the Ceiling Hoist.
Operation notification	10mm Status LED (underside), colour; green Green: Transit Coupling detect the Ceiling Hoist due the Reed Sensors.
Control Board	CTS-002
Time completed action after activation.	~1.7 seconds
Input Voltage	24-28 V/DC, max 3,5 A (max 98 W)
Power Supply	PLS Power Supply (Mean Well 24V/DC)
Switch-off time when not in use	NA
Weight (inclusive Safety Lock)	12,2 kg
Sound level (operation)	45 dB (A)
IP-rating	IP-32
Colour	RAL 9010
UDI Code	8720165793068
Disassembly Height	Split cover: 5 mm Standard cover: 45 mm
Dimensions (mm)	See next page



